



ENGLISH

Datasheet

2491X Equipment Wire 0.75mm²

RS Stock number **361-642**



Conductor: 24/0.20mm Plain Annealed Copper
(Class 5 to IEC 60228)

Insulation: PVC (Type TI1 to BS EN 50363)

**Insulation Radial
Thickness:** 0.60mm

**Diameter Over
Insulation:** 2.70mm (Maximum)

Voltage Rating: 300/500V

Conductor Resistance: 26 Ω /km @ 20°C
(Nominal)

Cable Weight: 11.8 kg/km (Nominal)

Standard: BS EN 50525-2-31