



PRODUCT-DETAILS

AL28/M25/C90/BL

90D PA66 FITTING M25 28MM-BL



General Information

Extended Product Type	AL28/M25/C90/BL
Product ID	7TCA296000R0807
EAN	5020963012846
Catalog Description	90D PA66 FITTING M25 28MM-BL
Long Description	90 Degree Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 28mm, M25 Thread, Polyamide (Nylon) 66, Black

Additional Information

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

Ordering

EAN	5020963012846
UPC	786210280172

Technical

Number of Batteries	0
Color	Black
Material	Polyamide/Nylon 6.6
Size	NC 28mm

Environmental

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963012846
Package Level 1 Height	2 in 51 mm
Package Level 1 Depth / Length	1.8 in 46 mm
Package Level 1 Width	2 in 51 mm

Certificates and Declarations

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

External Classifications and Standards

ETIM 8	EC001176 - Screw connection for corrugated plastic hose
ETIM 9	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

