1624 : Grooving machine









Description

It fits most machines currently on the market.
Designed for on site applications.
Fast and easy grooving to be carried out.
Quick, simple adjustment system ensuring a constant groove depth.
Turn with a ratchet wrench (1/2" ref. 220410) or handle for reduced effort.

Pipe for grooving:
Steel pipes: NF EN 10208.2/10255W/10217.1/10255S/10216.1.
Max thickness 5.5 mm.

Capacity: 1" to 6".

162400 supplied with:
- 1 connecting shaft,
- 1 set of rollers 2" to 6".

Adaptor optional.

References

Sku	Description	Capacity "	kg
162400	Grooving machine	2 - 6	11,000
162431	Set of rollers	1	2,300
162432	Set of rollers	1.1/4 - 1.1/2	2,400
162433	Set of rollers	2 - 6	2,500

