

SEALS TS3

A Tough All-Weather Smartphone



WATERPROOF

IP-68 SUBMERSIBLE TO 2 METER FOR AN HOUR IN WATER



ACOUSTIC NOISE-CANCELLING TECHNOLOGY



RESISTANT TO SHOCK & VIBRATION

MIL-810G FOR TRANSPORT SHOCK AND THERMAL SHOCK



GPS NAVIGATION

EQUIPPED WITH HIGH PERFORMANCE GPS NAVIGATION



PROTECTION FROM DUST

IP-68 IMPERVIOUS TO DUST AND MICRO-PARTICLES



RESISTANT TO EXTREME TEMPERATURE

OPERATIONAL IN EXTREME TEMPERATURES RANGING FROM -20°C TO +60°C



RUGGED 5 MP WITH AUTO FOCUS

WATERPROOF CAMERA



THOUSANDS OF APPS AVAILABLE



ALTIMETER



PEDOMETER

Seals TS3 is ruggedized and fully-featured Android Smart phone with IP68 design and state-of-the-art technology, which has been tested and certified to the MIL-STD 810G methods and procedures. Seals TS3 increases efficiency, safety and work crew productivity in the toughest working conditions. It features integrated GPS capabilities and one-key-positioning function; It allows for the end user to send out longitude, latitudes and a pre-set message to the five pre-set phone numbers. The features of the TS3 such as the acoustic noise-cancelling technology application, Waterproof camera, Morse code signal, E-compass, Altimeter, Pedometer and torch to name but a few can help to keep vital work processes running smoothly and efficiently.

www.sealstech.co.uk

TECHNICAL SPECIFICATIONS

SEALS TS3

● RUGGEDIZATION

- Approved to the U.S. military standard MIL-STD 810G
- Dust-proof level: IP rating Grade 6, impervious to any external dust
- Water-proof level: IP rating Grade 8, operational in up to 2m of water for 1 hr
- Shockproof body offers ultimate outdoor protection
- Can be used in temperatures ranging from -20°C to +60°C
- Waterproof camera
- Extra-loud speaker

● KEY FEATURES

- HSDPA/WCDMA: 900/2100MHz or 850/2100MHz
- GSM/GPRS/EDGE: 850/900/1800/1900MHz
- GPS, AGPS
- One-key-positioning setting with SOS rescue feature
- Morse code signals (SOS)
- 5MP with auto focus camera
- LED torch light
- Micro SD card slot (up to 32GB)
- FM radio with speaker
- WIFI (WLAN)
- 3.5 mm stereo audio jack
- Micro-USB
- Bluetooth 4.0 with EDR

● OTHER FEATURES

- E-compass
- Torch
- Pedometer

- Acoustic noise-cancelling technology
- Measurements of atmospheric pressure & temperature
- Indicator light
- Proximity sensor
- Motion sensor
- Light sensor
- PC connection

● PHYSICAL CHARACTERISTICS

- Dimensions: 125 x 65 x 17.4mm
- Weight: 207g (with battery)
- Display: 3.5-inch HVGA 320x480 capacitive touch screen
- Storage: 512MB RAM+512MB ROM

● CORE PLATFORM

- CPU: 650MHz
- Operating System: Android 2.3.6

● BATTERY

- Rechargeable lithium-ion 1780 mAh
- Stand-by time: GSM 950hrs , WCDMA 810 hrs
- Talk time: GSM 26 hrs, WCDMA 20 hrs

● ACCESSORIES

- Stereo earphone
- Screw driver
- Electrical wall charger
- CD manual
- Quick start guide
- USB cable