

Air Compressor XGT®

AC001G

40Vmax, 7.6 L

Model AC001G is a cordless air compressor powered by 40Vmax XGT® Li-Ion battery

This model is a portable air station for regular pressure tools. The main features and benefits are: Developed mainly for interior nailing applications such as finish nailing with 18Ga nail, Low noise level, yet with excellent combination of high air flow and lightweight design.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	2075 min ⁻¹
Maximum Flow Rate	34 L/min
Max Pressure	9,3 bar
Operating pressure	7,2 - 9,3 bar
Air Tank Capacity	7,6 L
Tool weight with battery	11,6 - 12,8 kg
Product net weight	10,9 kg
Product Dimensions (L x W x H):	302 x 434 x 382 mm

User benefits

- Battery protection system automatically shuts off power when the battery level is low
- Lightweight for easy portability



Related products

Other

User manual

Parts drawing