



33774 - Circline Lamps Item Detail



Subcategory	Circline Lamps
Product Code	33774 
Description	FC8T9/CW
Watts	22
Lumens (Initial)	1100
Lumens (Mean)	825
Average Life Hours	12000
Color Temperature (K)	4100
CRI	60
Bulb	T9
Base	4 Pin (G10q)
Nominal Length (In.)	8.2500
Nominal Length (mm)	210.000
Case Quantity	12
Additional Information	Cool White

General

Product Code	33774 
Description	FC8T9/CW
Subcategory	Circline Lamps

Physical

<u>Base Type</u>	4 Pin (G10q)
<u>Bulb Type</u>	T9
Bulb Material	Hard Glass
Bulb Nominal Diameter in inches	1.120
Nominal Length in inches	8.25
Max bulb diameter	1.22
Min bulb diameter	1.03
Min. Outside Lamp Diameter	8.00
Max. Outside Lamp Diameter	8.50
Min. Inside Lamp Diameter	5.81
Max. Inside lamp diameter	6.19

Photometric

<u>Color Temperature (K)</u>	4100
<u>CRI</u>	60
<u>Initial Lumens</u>	1100

<u>Mean Lumens</u>	825
<u>Nominal Efficacy (Lumens/Watt)</u>	50
Average Rated Life (hrs) 3hr cycle	12,000

Electrical

Dimmable (yes/no)	y
Max Cathode Resistance Ratio (Rh/Rc)	6.50
Min Cathode Resistance Ratio (Rh/Rc)	4.25
Minimum Starting Temp (deg F)	50
Nominal Lamp Amps	0.3700
Nominal Lamp Operating Frequency (Hz)	60
Nominal Lamp Volts	61

<u>Watts</u>	22
Max. Current Crest Factor	1.70
Min. Terminal to Terminal Starting Lamp Voltage (Vrms)-Rapid Start at 10°C	180.00
<u>Average Life Hours</u>	12000

Miscellaneous

DoE regulated (yes/no)	n
TCLP Regulated	n
<u>Additional Information</u>	Cool White

[Set the current view to the default view](#)