

378A Lever-operated grease gun



- Grease cartridge.
 - Pressure: 400 bar. Air bleed facility.
 - Use with cartridge or bulk grease.
 - Capacity 500 cm³, i.e. 400 g grease.
 - Hose compliant with DIN 1283 standard (static and burst pressure).
 - Hose built in rubber approved by DIN 20024 standard.
 - Hose diameter: 13.1 mm.
 - Hose radius of curvature: 90 mm.
 - Length: 370 mm excluding hose.
- Weight: 1.356 kg.