



17031-311 Trousers with holster pockets

Dyneema® - ULTIMATE STRETCH - lightweight

MASCOT® ADVANCED



92% polyamide/8% elastane

235 g/m²



ULTIMATE STRETCH. Shrinkage max. 2%.

Industrial care category C2



- Ultimate stretch material provides unique freedom of movement and high comfort.
- The water-repellent multifunctional stretch material combines a low weight with a very high durability.
- Well-designed holster pockets of durable CORDURA® can easily be zipped off when not in use, if they have to be emptied, or if the trousers need to be washed.
- The stretch kneepad pockets are made with a combination of CORDURA®, Kevlar® and the exceptionally durable fibre, Dyneema®.
- Excellent ventilation at the knee area via a zipper on the side of the leg.
- Extra visibility with the help of reflectors.
- To achieve the best possible comfort, we recommend that you choose MASCOT® Waterloo kneepads for this model.
- Co-certified for use with MASCOT kneepad type, LONG.

Technical info

Has a water-repellent finish. Ultimate stretch fabric that is lightweight and highly durable. The fabric is hardly felt against the skin as the pockets are integrated in the design. Double stitched seams on leg and crotch. Low waist. Ergonomically formed trouser leg. Belt loops. Fly with zip. Detachable holster pockets of durable CORDURA® - the outermost section of the right holster pocket is reinforced at the bottom with puncture resistant Kevlar®. Front pockets. Back pockets. Tool strap at both sides of waist. Thigh pocket with phone pocket with magnetic fastening and integrated ID card holder. Detachable ID card holder. Ruler pocket of CORDURA® with extra pockets. Durable and puncture resistant kneepad pockets of CORDURA®/Kevlar®/Dyneema®, elasticated and ventilated. Press stud adjustment at foot. Reflectors. We recommend



Certifications



Logo

As the product is made of stretch material, a stretchable transfer must be used when printing on the product.

Logo placement:

- Workwear logo stretch. Left back pocket. Max 11x8 cm/4.7x3.9 inches
- Workwear logo stretch. Right back pocket. Max 11x8 cm/4.7x3.9 inches
- Workwear logo stretch. Vertical on left thigh, read from the bottom upwards. Max 20x5 cm/7.8x1.9 inches
- Workwear logo stretch. Vertical on right thigh, read from the top downwards. Max 20x5 cm/7.8x1.9 inches
- Workwear logo stretch. Horizontal on right thigh. Max 11x6 cm/4.3x2.3 inches
- Workwear logo stretch. Left thigh horizontal. Max 11 x 6 cm/4.3x2.3 inches
- Workwear logo stretch. Horizontal on left calf. Max 11x6 cm/4.3x2.3 inches
- Workwear logo stretch. Horizontal on right calf. Max 11x6 cm/4.3x2.3 inches
- Workwear logo stretch. Vertical on left calf, read from the bottom upwards. Max 25x8 cm/9.8x3.1 inches
- Workwear logo stretch. Vertical on right calf, read from the top downwards. Max 25x8 cm/9.8x3.1 inches
- Workwear logo. Inside waistband. Max 15x1 cm/5.9x0.3 inches
- Workwear logo. Special placement. Contact to discuss further

00718-100, 50451-916 & 20118-915 kneepads for this model.
Co-certified together with kneepad type LONG in accordance
with EN 14404.

User

