




Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # 360050-1
090 DIA CLSTR BLK




TE Part # 1217262-1
HSG .090 CLUSTER BLOCK NAT




TE Part # 62131-8
CLSTR PIN RCPT



TE Part # 235280-6
CLUSTER BLOCK HSG .090 DIA




TE Part # 284406-3
CLUSTER BLOCK HSG .090 DIA. RE



KIT
TE Part # 7-2150436-7
OCEAN_2.0_SPARE_PART_KIT-110F140F




TE Part # 2150436-2
OCEAN_2.0_APPLICATOR-E-110F140F-REA



TE Part # 360033-1
090 DIA CLSTR BLK



TE Part # 1380145-1
CLUSTER BLOCK HSG. .090 DIA.



TE Part # 141101-2
RECEPT CLUSTER



TE Part # 1217263-1
HSG .090 CLUSTER BLOCK NAT



TE Part # 521078-1
CLUSTER BLOCK HSG 090DIA WHT

Customers Also Bought



TE Part #2160743002
55A0111-24-3



TE Part #130550
SOLIS 8 R M6



TE Part #130554
SOLIS 6 R M6



TE Part #825440-4
MOD 2 PINHDR 2X04P.



TE Part #7-1393239-3
RT31L012



TE Part #1744036-4
04P ECONOMY POWER .200 CL HSG



TE Part #1744417-8
8 POS EP 2.5 HSG, GLOW WIRE



TE Part #2120743-2
MAG-MATE Slim Line with Multispring



Documents

Product Drawings

CLSTR PIN RCPT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_62131-3_AW.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_62131-3_AW.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_62131-3_AW.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Magnet Wire Terminals & Splices

English

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English