





| LOC | DIST | REVISIONS |     |                           |         |     |      |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
|     |      | P         | LTR | DESCRIPTION               | DATE    | DWN | APVD |
| GP  | 00   |           | F1  | REVISED PER ECO-11-004835 | 11MAR11 | RK  | HMR  |



## RECOMMENDED PCB LAYOUT

|       |       |    |    |             |
|-------|-------|----|----|-------------|
| 3.300 | 2.900 | 29 | 60 | 1-5103311-2 |
| 2.800 | 2.400 | 24 | 50 | 1-5103311-0 |
| 2.500 | 2.100 | 21 | 44 | 5103311-9   |
| 2.300 | 1.900 | 19 | 40 | 5103311-8   |
| 2.000 | 1.600 | 16 | 34 | 5103311-7   |
| 1.600 | 1.200 | 12 | 26 | 5103311-6   |
| 1.300 | .900  | 9  | 20 | 5103311-5   |
| 1.100 | .700  | 7  | 16 | 5103311-3   |
| 1.000 | .600  | 6  | 14 | 5103311-2   |
| .800  | .400  | 4  | 10 | 5103311-1   |

| C | B | A | NO<br>OF<br>POSN | PART<br>NUMBER |
|---|---|---|------------------|----------------|
|---|---|---|------------------|----------------|

|                                                                                                   |  |                                                                                                                             |  |                                                                                                       |  |
|---------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                            |  | DWN: 03 NOV 05<br>B. LATTUCA<br>CHK: 03 NOV 05<br>S. BOLASH                                                                 |  |  TE Connectivity |  |
| DIMENSIONS:<br>INCHES                                                                             |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ± -<br>1 PLC ± -<br>2 PLC ± -.005<br>3 PLC ± -<br>4 PLC ± -<br>ANGLES ± ± - |  | NAME<br>HEADER ASSY, RIGHT ANGLE, LOW PROFILE,<br>AMP - LATCH<br>-                                    |  |
|              |  | APVD: 03 NOV 05<br>M. WALMSLEY<br>PRODUCT SPEC<br>108-40018<br>APPLICATION SPEC<br>-                                        |  | SIZE<br>A1                                                                                            |  |
| MATERIAL<br> |  | FINISH<br>                             |  | DRAWING NO<br>00779 © 5103311                                                                         |  |
|                                                                                                   |  | WEIGHT<br>-                                                                                                                 |  | RESTRICTED TO<br>-                                                                                    |  |
| CUSTOMER DRAWING                                                                                  |  |                                                                                                                             |  |                                                                                                       |  |
|                                                                                                   |  |                                                                                                                             |  | SCALE 4:1 SHEET 1 OF 1 REV F1                                                                         |  |