

Product Datasheet

Unheated safety shower with stainless steel open bowl eye wash

EXP-18GS/85G

EXP-18GS/85G-PC

Ensure you are prepared in the event of an emergency. This floor mounted shower is combined with a stainless steel open bowl eye/face wash for a complete safety solution. The high flow rate shower nozzle provides an even spray pattern with a 76 litre per minute flow rate to remove contaminants effectively. For improved corrosion resistance the eye wash is constructed from stainless steel and features dust covers to protect the nozzles from dust and debris.

Meets the requirements of EN15154 and ANSI Z358.1-2014.

Supplied with safety shower and eye wash sign.



Specifications

MATERIALS OF CONSTRUCTION	
PIPEWORK & FITTINGS	Stainless steel (GS) or powder coated stainless steel (PC)
OPERATING VALVE	Stainless steel, full bore, stay open ball valve
SHOWER NOZZLE	Injection moulded nylon 6
EYE WASH	Stainless steel
EYE WASH DIFFUSERS	Chrome plated brass retaining ring, stainless steel filter mesh, plastic body
STANDARD FINISH	Polished brush (GS) or green powder coated (PC)
SERVICES	
WATER INLET	1¼" female BSP
OPERATING PRESSURE	2 to 6 BAR G / 29 to 87 PSI (higher supply pressures accommodated with the incorporation of the optional pressure reducing valve)
MINIMUM FLOW RATES	Shower: 76 L per minute / 20 US gal per minute Eye wash: 12 L per minute / 3 US gal per minute
AMBIENT OPERATING TEMPERATURE	
MINIMUM	5C / 41F
MAXIMUM	35C / 95F
OPERATION	
SHOWER	Pull handle
EYE WASH	Push plate
DIMENSIONS & WEIGHT	
DIMENSIONS (WxDxH)	308mm (12.1in) x 782mm (30.8in) x 2297mm (90.4in)
WEIGHT	16kg (35lb)

General Arrangement Drawing

Unheated safety shower with stainless steel open bowl eye wash

EXP-18GS/85G

EXP-18GS/85G-PC

