



# Product data sheet

Power tools for trade & industry

Optical Level

## PRO GOL 32 D



Robust and reliable – ideal for outdoor use

### The most important data

Unit of measure	360 degrees
Magnification	32 x
Accuracy	± 1.0 mm at 30 m

**Order number** 0 601 068 502

## Technical data

### Additional data

Dust and splash protection	IP 54
Unit of measure	360 degrees
Magnification	32 x
Accuracy	± 1.0 mm at 30 m
Tripod thread	5/8"
Working range	120 m
Operating temperature	-10 – 50 °C
Storage temperature	-20 – 70 °C
Weight, approx.	1.5 kg
Working range, value	120 m



**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

---

## Advantages:

- Ideal for outdoor use due to a robust housing with dust and splash protection (IP54)
- Fast aperture for a sharp image of the target
- Compensator lock for safe transport



---

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/eg/en/wac/>

