M. K. JUCHHEIM Gmbh & Co

36035 Fulda
Germany

Phone (0661) 60 03 - 0
Telex 49 701
Fax (0661) 60 03 - 607

For United Kingdom:
Jumo Instrument Co. Ltd.

Temple Bank
Riverway, Harlow,
Essex CM20 2TT
Phone (01279) 63 55 33
Fax (01279) 63 52 62

For USA:
Jumo Process Control Inc.

735 Fox Chase
Coatesville, PA 19320
Phone 610 - 380 - 8002,
800 - 554 JUMO
Fax 610 - 380 - 8009

JUMO

MEASUREMENT AND CONTROL

Push-in Resistance Thermometer with 0.25 mm² coiled cable with PUR insulation

RS 158-5271

Fitting length EL in mm	Temperature in °C	Type 1 x Pt 100	Type 2 x Pt 100
Protection tube stainless steel X 5 CrNi 18 12, Material Ref. 1.4303			
50	–5 +105	90 275-F07 ●	—



● available from stock

902105

Item 4

Push-in Resistance Thermometer with 0.35 mm² cable with stainless steel braiding

Fitting length EL in mm	Temperature in °C	Type 1 x Pt 100	Type 2 x Pt 100
Protection tube stainless steel X 6 CrNiMoTi 17 12 2, Material Ref. 1.4571			
60	–5 +350	90.285-F45 ●	90D285-F45



● available from stock

902105

Item 5

Subject to modification.