

FEATURES

- **Flexible design:** Easily adapts to different shapes and surfaces, making installation simple.
- **IP54 rating:** Offers protection against dust and water splashes, suitable for indoor and some outdoor applications.
- **Warm white LED colour:** Creates a comfortable and inviting lighting environment.
- **60 LEDs per metre:** Ensures consistent and bright illumination throughout the strip.
- **4.8 W/m power consumption:** Energy-efficient operation reduces electricity costs.
- **12 V dc voltage:** Compatible with standard low-voltage power supplies.
- **16.6 mm LED pitch:** Provides uniform light distribution without dark spots.

RS PRO Flexible LED Strip Light, 5m Warm White

RS Stock No: 558-393



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible LED strip light offers a versatile lighting solution ideal for both residential and commercial environments. With a warm white hue, it provides a cosy and inviting atmosphere. The strip is designed for easy installation and can be adapted to various spaces due to its flexibility.

General Specifications

Colour Temperature	2700-3500 K
Flexible/Rigid	Flexible
LED Colour	Warm White
LED Pitch	16.6 mm
Number of LEDs Per Metre	60
Product Type	LED Strip Light
Typical Luminous Flux (lm/m)	360 lm/m

Protection Category

IP Rating	IP54
-----------	------

Electrical Specifications

Power Per Metre	4.8 W/m
Voltage	12 V dc

Approvals

Standards/Approvals	CE, RoHS
---------------------	----------

Mechanical Specifications

Strip Length	5 m
Strip Width	8 mm