

FEATURES

- **Sintered Bronze Material:** Provides high durability and resistance to wear, ensuring long service life
- **Flanged Design:** Offers easy installation and secure positioning in applications
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads without deformation
- **0.62 in Bore Size:** Compatible with a wide range of shafts for versatile use
- **0.75 in Outside Diameter:** Fits standard housings for seamless integration
- **1 in Width:** Ensures stability and support in various applications

RS PRO 0.62 in Flanged Plain Bearing

RS Stock No: 528-225



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, it offers excellent durability and reduced friction, making it ideal for various industrial uses. Its compact design allows for easy integration into machinery, enhancing performance and longevity.

General Specifications

Bore Size	0.62 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	0.75 in
Width	1 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

