



PRODUCT DATASHEET

Datasheet creation date: 2025/07/08 2:32 (UTC)



6000ZZ

Single-Row Deep Groove Ball Bearings

Parts Number

6000ZZC3

Boundary Dimensions

d	10	mm	Bore diameter
D	26	mm	Outside diameter
B	8	mm	Width
r (min.)	0.3	mm	Chamfer dimension

Basic Load Ratings

Cr	5050	N	Basic dynamic load rating
C0r	1970	N	Basic static load rating

Speeds

Grease	30000	min-1	Grease lubrication
--------	-------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	12	mm	Diameter of shaft abutment
da (max.)	13	mm	Diameter of shaft abutment
Da (max.)	24	mm	Diameter of housing abutment
ra (max.)	0.3	mm	Radius of shaft or housing fillet
Dx (min.)	0	mm	Diameter of snap ring recess in the housing
Cy (max.)	0	mm	Distance from outer ring side face to snap ring back face

Calculation factors

fo	12.4	Factor
----	------	--------

Additional information

z	7	Number of Balls	
Dw	4.762	mm	Ball Diameter

Mass

Mass approx.	0.018	kg	Mass approx.
--------------	-------	----	--------------

