



# Product data sheet

Power tools for trade & industry

Wet/Dry Extractor

## GAS 35 H AFC



H-Class versatile wet/dry dust extractor with automatic filter cleaning developed for hazardous dust

### The most important data

|                       |                       |
|-----------------------|-----------------------|
| Weight                | 12.4 kg               |
| Container volume, net | 23 l                  |
| Filter surface area   | 5,000 cm <sup>2</sup> |

**Part Number** 0 601 9C3 660

[> More product information](#)

## Technical data

### Technical data

|                                 |                       |
|---------------------------------|-----------------------|
| Rated input power               | 1,200 W               |
| Weight                          | 12.4 kg               |
| Container volume, gross         | 35 l                  |
| Container volume, net           | 23 l                  |
| Container volume, net, water    | 19.2 l                |
| Dust class of wet/dry extractor | H                     |
| Dust class                      | H                     |
| Tool dimensions (width)         | 375 mm                |
| Tool dimensions (length)        | 515 mm                |
| Tool dimensions (height)        | 575 mm                |
| Filter surface area             | 5,000 cm <sup>2</sup> |
| Max. airflow rate (turbine)     | 74 l/s                |
| Max. vacuum pressure (turbine)  | 254 mbar              |
| Wheels, number                  | 4                     |



# Product data sheet

Power tools for trade & industry

---

## Advantages:

- H-class certified for carcinogenic and pathogenic dust, increasing user protection
- Automatic filter cleaning mechanism for constant working
- Flow control monitoring constant air flow through the suction cup, including an acoustic warning signal

