

HIGH PRECISION DRILLING IN MULTIPLE MATERIALS

EXPERT CYL-9 Multi Construction Drill Bit

EXPERT

- ① Accurate drilling is easier with Bosch Centering Geometry
- ② Start holes accurately with a specially designed centring tip
- ③ High-performance carbide tip manufactured by fine grinding
- ④ Optimised dust extraction channel for fast, efficient drilling



CENTERING
GEOMETRY

UP TO
5x*



* vs. Bosch CYL-3



BOSCH

EXPERT CYL-9 MULTI CONSTRUCTION DRILL BIT



- Ideal for drilling holes into multiple materials. Can be used in impact mode on concrete and stone, and on rotary setting for brick, soft ceramic tile, sheet metal, wood and plastic
- Best for building trades: maximum precision and highly versatile
- Up to 5x more precise than a Bosch CYL-3 Drill Bit
- Cylindrical shank compatible with three-jaw drill chucks



PRODUCT PROPERTIES				ORDERING INFORMATION				
	Diameter (D) mm	Working length mm	Total length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number
Pack of 1								
	3.00	40	70	PC1d	1	5	538 938	2 608 900 600
	3.50	40	70	PC1d	1	1	538 952	2 608 900 602
	4.00	40	75	PC1d	1	5	538 976	2 608 900 604
	4.00	80	130	PC1d	1	5	538 983	2 608 900 605
	5.00	50	85	PC1d	1	5	538 990	2 608 900 606
	5.00	90	150	PC1d	1	5	539 003	2 608 900 607
	5.50	50	85	PC1d	1	5	539 027	2 608 900 609
	5.50	100	150	PC1d	1	5	539 034	2 608 900 610
	6.00	60	100	PC1d	1	5	539 041	2 608 900 611
	6.00	90	150	PC1d	1	5	539 058	2 608 900 612
	6.00	200	250	PC1d	1	1	596 488	2 608 901 481
	6.50	60	100	PC1d	1	5	539 089	2 608 900 615
	6.50	90	150	PC1d	1	5	539 096	2 608 900 616
	6.50	200	250	PC1d	1	1	596 495	2 608 901 482
	7.00	60	100	PC1d	1	5	539 119	2 608 900 618
	7.00	90	150	PC1d	1	5	539 126	2 608 900 619
	7.00	200	250	PC1d	1	1	596 501	2 608 901 483
	8.00	80	120	PC1d	1	5	539 140	2 608 900 621
	8.00	90	150	PC1d	1	5	539 157	2 608 900 622
	8.00	200	250	PC1d	1	1	596 518	2 608 901 484
	9.00	80	120	PC1d	1	5	539 188	2 608 900 625
	10.00	80	120	PC1d	1	5	539 195	2 608 900 626
	10.00	90	150	PC1d	1	5	539 201	2 608 900 627
	10.00	200	250	PC1d	1	1	596 525	2 608 901 485
	11.00	90	150	PC1d	1	5	539 232	2 608 900 630
	12.00	90	150	PC1d	1	5	539 249	2 608 900 631
	12.00	200	250	PC1d	1	1	596 549	2 608 901 486
	14.00	150	200	PC1d	1	1	596 556	2 608 901 487
	14.00	200	250	PC1d	1	1	596 570	2 608 901 488
	16.00	150	200	P1c	1	1	596 594	2 608 901 489
Pack of 8								
	10.00	80	120	P1h	8	1	539 379	2 608 900 644
Pack of 10								
	4.00	40	75	P1h	10	1	539 300	2 608 900 637
	5.00	50	85	P1h	10	1	539 317	2 608 900 638
	5.50	50	85	P1h	10	1	539 324	2 608 900 639



BOSCH

EXPERT CYL-9 MULTI CONSTRUCTION DRILL BIT

PRODUCT PROPERTIES				ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number	
6.00	60	100	P1h	10	1	539 331	2 608 900 640	
7.00	60	100	P1h	10	1	539 355	2 608 900 642	
8.00	80	120	P1h	10	1	539 362	2 608 900 643	



BOSCH