

Freecom DataBar USB 2.0



Slimline Design

The Ultimate Floppy Replacement!

Freecom DataBar USB 2.0

- External USB 2.0 storage device that works like a hard drive.
- Save, access and share data with colleagues and friends.
- Slimline design allows direct placement next to other USB devices
- Easy installation, no drivers needed*, USB port bus-powered!
- Available in capacities from 64MB up to 512MB.
- Compatible with PC, notebook and Mac allowing cross platform file sharing.
- Ideal for storing and sharing digital pictures, music files, text files, spreadsheets & presentations.
- 2 years manufacturers warranty.

Introducing Freecom DataBar: Access your files anytime. Anywhere!

Freecom DataBar provides the ultimate mobile storage solution for people on the go. Working on a presentation, a document or e-mails and need to take them with you? No problem! Want to share new MP3 files or digital pictures with your friends? It is really easy! Simply copy the files onto DataBar and take them with you. To access your data, simply plug DataBar into any PC or MAC – without the need for software drivers, bulky cables or adapters. DataBar is actually your perfect floppy replacement. Access your files. Anytime. Anywhere. Keep it simple!

Use what	Store what	DataBar 64MB	DataBar 128MB	DataBar 256MB	DataBar 512MB
Word Documents	Text page	2250 pages/files	4500 pages/files	9000 pages/files	18000 pages/files
Digital Pictures	1600x1200 pixel	200	400	800	1600
Music Files	64KB/s	2 hours (30 songs)	4 hours (60 songs)	8 hours (120 songs)	16 hours (240 songs)
Floppy Disk	Floppy 1.44MB	44 floppy's	88 floppy's	176 floppy's	352 floppy's



WWW.FREECOM.COM

Freecom
Keep it simple

Freecom DataBar USB 2.0

Product specifications	Freecom DataBar USB 2.0 storage device
Storage capacity	64MB, 128MB, 256MB, 512MB
Interface	USB 2.0; can also be connected to USB 1.1 port
Data transfer rate	8MB/s (read) / 7MB/s (write)
Data retention	up to 10 years
Dimensions	65.2 x 19.6 x 9.2 mm / 2.6 x 0.8 x 0.4 inch (with cap)
Weight	9 gr. / 0.32 ounce
Led indicator	LED indicates read write access.
Power requirements	USB bus powered (4.4V ~ 5.25V) (no AC adapter needed!)
Environmental specifications	Operating temperature: 0° C / 45° C / Storage temperature: -20°C / 60° C
OS Support	Windows 98SE*/ME/2000/XP, MAC OS 9.1 10.x, Linux 2.4.X which support USB mass storage protocol
EMI compliance	CE, FCC, EMI, EMS
Package includes	<ul style="list-style-type: none"> • Freecom DataBar USB2.0 Stick • Quick Install Guide (in 6 languages: UK, D, NL, F, I, E) • Two years manufacturers warranty

*Windows 98SE software driver; please visit our website: www.data-bar.com

	64 MB USB 2.0	128 MB USB 2.0	256 MB USB 2.0	512 MB USB 2.0
Art. No. EU/UK	23852	23853	23854	23855
EAN code EU/UK	4021801238528	4021801238535	4021801238542	4021801238559
UPC	7-09939-23852-1	7-09939-23853-8	7-09939-23854-5	7-09939-23855-2
Color	Black	Black	Black	Black

