

PRODUCT-DETAILS

# DS201 M C6 A300

## DS201 M C6 A300 - RCBO



### General Information

Extended Product Type	DS201 M C6 A300
Product ID	2CSR275140R3064
EAN	8012542113355
Catalog Description	DS201 M C6 A300 - RCBO
Long Description	The DS201 series RCBO is a 1P+N in two-modules device for the protection of end user single-phase circuits against overload and short-circuit currents; protection against the effects of sinusoidal alternating and direct pulsating earth fault currents; protection against indirect contacts and additional protection against direct contacts (with sensitivity = 30 mA).

### Technical

Standards	IEC 61009-1 IEC 61009-2-1 EN 61009-1 EN 61009-2-1
Type of Residual Current	A type
Number of Poles	1+N
Number of Protected Poles	1
Rated Current ( $I_n$ )	6 A
Rated Voltage ( $U_r$ )	230-240 V AC
Rated Insulation Voltage	500 V

(U<sub>I</sub>)

Overvoltage Category	III
Pollution Degree	2
Rated Frequency (f)	50...60 Hz
Rated Short-Circuit Capacity (I <sub>cn</sub> )	(230 / 400 V AC) 10 kA
Rated Ultimate Short-Circuit Breaking Capacity (I <sub>cu</sub> )	10 kA
Tripping Characteristic	C
Energy Limiting Class	3
Electrical Endurance	10000 cycle 20000 cycle
Degree of Protection	IP2X
Connecting Capacity	Busbar 10 mm <sup>2</sup> Rigid 25 ...25 mm <sup>2</sup> Flexible 25 ...25 mm <sup>2</sup>
Power Supply Connection	Arbitrary
Position of Neutral Terminals	Right
Power Loss	4.4 W

## Environmental

Ambient Air Temperature	Operation -25...55 °C
RoHS Status	Following EU Directive 2011/65/EU

## Technical UL/CSA

Short-Circuit Current Rating (SCCR)	0.3 A
-------------------------------------	-------

## Dimensions

Product Net Width	0.035 m
Product Net Height	0.085 m
Product Net Depth / Length	0.069 m
Product Net Weight	0.239 kg

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.040 m
Package Level 1 Height	0.106 m
Package Level 1 Depth / Length	0.080 m
Package Level 1 Gross Weight	0.225 kg
Package Level 1 EAN	8012542113355

Package Level 2 Units	5 piece
Package Level 2 Width	0.200 m
Package Level 2 Height	0.106 m
Package Level 2 Depth / Length	0.080 m
Package Level 2 Gross Weight	1.125 kg
Package Level 2 EAN	8012542113362

---

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363010
Replacement Product ID (NEW)	2CSR275180R3064

---

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5588
Environmental Information	refer to RoHS information
Instructions and Manuals	9AKK106354A0766
RoHS Information	2CSC422002K2701

---

## Popular Downloads

Data Sheet, Technical Information	2CSC400002D0209
Instructions and Manuals	9AKK106354A0766

---

## Classifications

Object Classification Code	Q
ETIM 4	EC000905 - Earth leakage circuit breaker
ETIM 5	EC000905 - Earth leakage circuit breaker
ETIM 6	EC000905 - Earth leakage circuit breaker
ETIM 7	EC000905 - Earth leakage circuit breaker

---

## Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Circuit Breakers with Overcurrent Protection RCBO

