

### Main

Range	New Unica
Device application	Mounting
Product or component type	Mounting box
Aesthetic name	Unica Pro
Number of modules	8 modules 6 modules 3 x 2 modules
Number of gangs	3 gangs
Fixing mode	Screws

### Complementary

Device mounting	Surface
Cable entry	6 knock-outs
Material	ABS (acrylonitrile butadiene-styrene): box
Standards	IEC 60669-1 IEC 60884-1
Depth	40 mm
Width	229 mm
Height	87 mm
Net weight	0.114 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

### Environment

IK degree of protection	IK04
-------------------------	------

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations