



ENGLISH

Datasheet

IP66 Wall Box with Plain Door, 304 Stainless Steel, Unpainted, 400 x 600 x 200mm

RS Stock number 758-6952



IP66 Wall Boxes

A range of IP66 wall boxes with a brushed finish made from AISI 304 stainless steel. These enclosures have a new double lip edge to ensure higher strength and ease of installation for the panel builder/end user.

AISI 304 grade stainless steel sheets

Double lip edges

IP66 protection

Door is removable and opens 120°. Fitted with polyurethane gasket

Supplied with stainless steel hinges, double wing lock and key and stainless steel wall brackets

IP66 protection

Body Material	304 Stainless Steel
Chassis Plate	No
Colour	Natural
Door Type	Plain
External Depth	200mm
External Dimensions	400 x 600 x 200mm
External Height	400 mm
External Width	600 mm
Fixing Kit	No
Gland Plate	No
IP Rating	IP66