



KB363A

Insulated busbar 3P 63A prong 10mm² 12M

Technical Characteristics

Architecture

Number of poles	3 P
-----------------	-----

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Rated current	63 A
---------------	------

Voltage

Max operating voltage	400 V
-----------------------	-------

Rated impulse withstand voltage	4 kV
---------------------------------	------

Dimensions

Length	210 mm
--------	--------

Capacity

Number of modules	12
-------------------	----

Materials

Colour	brown
--------	-------

Connection

Connection cross-sect. rigid cable	10mm ²
------------------------------------	-------------------

Type of connection	with screw
--------------------	------------

Standards

European directive WEEE	concerned
-------------------------	-----------