



Sample photo

Order symbol: ABS 200/100 HG
Product nbr: 6081327
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074023001
El. number:
 Finland: 3420573
 Denmark: 8212023330
 Italy: 7361125
 Sweden: 2535772
 Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Rating:
mm:	255	180	100	Ingress Protection (EN 60529): IP 66/67
inch:	10.0	7.1	3.9	Impact Resistance (EN 62262): IK 07

Materials:		Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes Flammability Rating (UL 746 C 5): UL 94 HB Glow Wire Test (IEC 695-2-1) °C: 650 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
Material:	ABS	
Base colour:	RAL 7035	
Cover colour:	RAL 7035	
Cover screws material:	Polyamide	
Cover screws colour:	Grey	
Gasket material:	TPE	

Temperatures:		Certificates:
Short term:	-40 ... 80 °C	Fimko
Continuous:	-40 ... 60 °C	Europe EN 62208: 2003
Short term:	-40 ... 175 °F	Gost R
Continuous:	-40 ... 140 °F	

Accessories:	
MIV 200	Mounting plate (Galvanized steel)
MIN 15	DIN-15 Mounting rail
MIN 20	DIN-15 Mounting rail
MIV 15	DIN-35 Mounting rail
MIV 20	DIN-35 Mounting rail
FP A 200/180	Front plate (Aluminium)
HFP 180	Front plate hinge series (2 pcs)
FP 22046	Wall fastening lug (4 pcs)

