



Cobalt 4 to 20 mm - 1 pc

COBALT ALCrN STEP DRILLS

- New Aluminium Chromium Nitride (AlCrN) coating for 10x more life vs. MILWAUKEE® standard step drill.
- For steel and stainless steel.
- RAPID STRIKE TIP™: Accurate start without walking and fast drilling without the need to pre-drill the material.
- Special tip and step geometry for jam-free performance - less risk of drill snagging when used with cordless tools and also prevents deformation of the drilled material.
- Optimised 2 flute ground sharpened edge geometry for 2 x faster and smoother cutting.
- With 3 flat secure grip to prevent step drill from slipping in the chuck and ensure maximum transmission of torque.
- Laser engraved size markings for best long term visibility.



Article Number	48899372
No. of steps	10
overall length (mm)	62
Pack quantity	1
Shank Diameter (mm)	8