

Datasheet

Star Precision Screwdriver -T-4 x 60 mm

RS Stock number 243-462



Specification:

Material:

Silicone chrome molybdenum vanadium steel (svcm 55) for screwdriver blades, Polypropylene/TPR handles

Finish:

Satin chrome finish for blade with phosphate black tip, black color TPR grip and red colour injection handle.

Hardness:

Heat treated to HRC: 55~59 for screwdriver blades

Contents:

1 pc – star driver precision screwdriver - t-4 x 60mm with black colour TPR grip and red p.p. injection shaft & handle length of blade: 60mm, overall length- 155 mm, remove the magnet from the steel blade

Feature:

Blades made from high grade Chrome – vanadium steel Rotating cap allows user to drive easily and adjust precisely Tri – lode shape of handle provides comfortable grip during rotation