



Mini Connector TH387 Plug-Socket 3P IP68

Article number: 145141

BAI Watertight Mini Connector TH387 Tee Straight Plug & Socket 1 way in - 1 way out 3 poles x 4mm² (max) 17.5A 500V/AC IP68 23x85mm Black

Waterproof IP68 mini cable connector equipped with male and female plug-in sockets. IMPORTANT: for safety reasons, the voltage may only be connected to the female plug-in socket. 2 pole + earth. Wire cross section (stripped cable) 0.5mm²-4.0mm². Cable diameter 7.0mm-12.0mm. Thermal resistance: -40°C +125°C.

General ETIM properties

ETIM group	Accessories for lighting
ETIM class	Electrical accessories/spare parts for luminaires
Name	Mini Connector TH387 Plug-Socket 3P IP68
Brand	Bailey
Productseries	Watertight connector
Producttype	TH387

ETIM specifications

Number of cores	3
Nominal cross section [mm²]	4
Length [mm]	85
Width [mm]	23
Height/depth [mm]	23
Type of accessory/spare part	Coupler/connector straight
Colour	Black
Accessory	Yes
Spare part	No
Supporting protocol for ZigBee	No