



DYNATECH® torque wrench with interchangeable round end

DYT-50-2
DYT-...

SAM Outillage

10 rue Camille de Rochetaillée
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 €

<https://www.sam-outillage.fr/>

Photos and texts not contractually binding. Do not litter. Document generated on 2023-10-26 12:37:00





DESCRIPTION

DYNATECH® torque wrench with interchangeable round end

GREATER PRODUCTIVITY: owing to a reduced immobilisation thanks to the high-strength ratchets. AN ALL-STEEL WRENCH: making it possible to withstand every type of working environment. LIMITED CALIBRATION ERRORS: via the setting with the easy-to-use vernier. EASY TO READ WHATEVER THE CONDITIONS: even in full sunlight thanks to the long-life black marking on the vernier. EASY-TO-USE TOOL: thanks to a direct, ergonomic grip. EJECTION OF THE BITS WITH A PUSHBUTTON: ensuring quick, easy changes.

Versatile, precise wrench for performing multiple interventions without having to change tool.

Repeatability guaranteed to ensure the safety of your tightening operations.

Utilisation of the wrench for loosening by turning the end fitting over.

ERGONOMIC:

Handle that withstands hydrocarbons, solvents, brake fluid and paraffin.

Efficient, comfortable grip for the operator, reducing risks of musculoskeletal disorders.

SAM Outillage

10 rue Camille de Rochetaillée
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 €

<https://www.sam-outillage.fr/>

Photos and texts not contractually binding. Do not litter. Document generated on 2023-10-26 12:37:00



COMFORT:

Scale in Nm with wide utilisation range, allowing you to have the right tool whatever the situation.

Wrench supplied with a 3-point calibration certificate in a plastic case or in a box depending on the number of accessories.

PRECISION:

Precision guaranteed to within +/- 3% for up to 5,000 cycles, i.e.

25% better than the requirements of standard ISO 6789-1 (except models with capacities of 1-5 Nm: +/- 6%).

New spring withstanding 1,000,000-cycle fatigue tests at each wrench's max.

torque value.

Mark on the handle for perfect positioning of the contact point ensuring precise tightening.

Each wrench is numbered and supplied with a verification report in compliance with standard NF EN ISO 6789-1.

Mechanical click-type torque wrench.

Type II - Class A.

STANDARDS / DIRECTIVES

NF ISO 3315, NF ISO 6789-1

SPECIFIC DATA

Designation	TORQUE WRENCH DYNATECH 10-50 NM FOR ROUND ENDS
Sales reference	DYT-50-2
Weight (kg)	2.7
Container	Box
Capacity (Nm)	10-50
Ratchet	3/8
double square	DC-0-3/8

SAM Outillage

10 rue Camille de Rochetaillée
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 €

<https://www.sam-outillage.fr/>

Photos and texts not contractually binding. Do not litter. Document generated on 2023-10-26 12:37:00



Graduation (Nm)	0,50
Ends	12 mm
only wrench length	345
Length with ratchet (mm)	382
Ratchet reference	TC-0-3/8
Dimensions containing (mm)	420 x 275 x 95
Guarantee	M

Guarantee applied

M1 | SAM Equipment and Machine Guarantee:

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

SAM Outillage

10 rue Camille de Rochetaillée
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 €

<https://www.sam-outillage.fr/>

Photos and texts not contractually binding. Do not litter. Document generated on 2023-10-26 12:37:00

