



CSB Twin Pack 165 x 24T/24T - 2pc

CIRCULAR SAW BLADES FOR HAND HELD CIRCULAR SAWS

- PTFE coating: Cuts cooler, non stick for quicker cuts. Protects against corrosion and accumulation of resin.
- Laser cut vibration slots: Low vibration and increased accuracy.
- High grade laser cut steel: Guaranteed accuracy.
- Premium cobalt infused tungsten carbide: Sharp and clean cuts.
- Thin Kerf: Cordless optimised, extra thin cutting width for maximum runtime
- All wood types: Soft/ hardwood, plywood, laminated chipboard, melamine, MDF
- **Standard blades without PTFE coating and vibration slots



All Wood Types	✓
Article Number	4932479836
Blade diameter (mm)	165
Bore size (mm)	5/8"
Contents	2 x 165x $\frac{5}{8}$ "x24 tooth, fast cut wood blade (4932471311)
Cutting width (kerf) (mm)	1.6/1.6
Materials suited for	Wood with nails & screws Green wood Wood Particleboard, Fibrecement board, Fibreglass
Pack quantity	2