



REF-PLUS-R50-K

SICK
Sensor Intelligence.



Ordering information

Type	Part no.
REF-PLUS-R50-K	4051185

Other models and accessories → www.sick.com/

Detailed technical data

Technical specifications

Accessory group	Reflectors
Accessory family	Reflective tape
Description	Self-adhesive, customizable length by roll
Mounting system type	Self-adhesive
Ambient operating temperature	-20 °C ... +60 °C
Dimensions	5 cm x 22.8 m ¹⁾

¹⁾ Customizable length by roll. Width 5 cm, length max. 22.8 m.

Classifications

ECI@ss 5.0	27279203
ECI@ss 5.1.4	27279203
ECI@ss 6.0	27279203
ECI@ss 6.2	27279203
ECI@ss 7.0	27279203
ECI@ss 8.0	27279203
ECI@ss 8.1	27279203
ECI@ss 9.0	27273601
ECI@ss 10.0	27273601
ECI@ss 11.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
UNSPSC 16.0901	39111827

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations www.sick.com