



### Main

Range	Spacial
Product or component type	Flexicable gland plate
Accessory / separate part category	Cable management accessory
Anwendung	Multi-purpose
Range compatibility	Spacial S3D
Mounting location	Enclosure bottom
Cable gland type	Pierceable by screwdriver
Type of gland plate	Membrane
Cable outer diameter	10...26 mm
Cable entry	Without
Device composition	1 plate membrane
Quantity per set	Set of 1
Material	Plate: steel Membrane: HCE (heat curable elastomer)

### Complementary

Colour	Plate: grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Height	30 mm
Width	495 Mm 510 mm real:
Depth	220 mm
Net weight	1.258 kg
Thickness	1.5 mm
Number of cut-out	Undrilled
Cut-out dimensions	428 x 63 mm

### Packing Units

Package 1 Weight	1.258 kg
------------------	----------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------