









# CONTRE-ÉCROU laiton



Couleur : revêtement nickelé  
 Matière : laiton  
 Norme : EN 50262  
 EN 60423  
 Guide UTE 68312

 métrique	 mm	 mm	Longueur de filetage	Code	
M12		15	3	D 4312 109	50
M 16		20	3	D 4316 107	50
M 20		24	3,5	D 4320 104	50
M 25		30	3,5	D 4325 109	20
M 32		35	4,5	D 4332 107	20
M 40		45	4,5	D 4340 102	20
M 50		55	5,5	D 4350 101	10
M 63		70	6	D 4363 101	5

 PG	 mm	 mm	Longueur de filetage	Code	
PG 07		15	2,9	D 4007 104	50
PG 09		19	2,9	D 4009 108	50
PG 11		21	3,1	D 4011 101	50
PG 13		23	3,1	D 4013 105	50
PG 16		26	3,1	D 4016 106	25
PG 21		32	3,6	D 4021 100	20
PG 29		41	4,1	D 4029 106	15
PG 36		51	5,1	D 4036 104	10
PG 42		60	5,1	D 4042 105	10
PG 48 NFC		64	6,1	D 4048 107	10
PG 48 DIN		64	5,6	D 4049 104	10