

Hard Polyurethane - TUH

TUH1288N-20

Datasheet

General Series Information

- Applicable tubing O.D.: Ø 4 to Ø 16 mm
- Operating temperature: -20 to 60 °C
- Colours: black, white, blue and translucent.

Standard specifications

Size	1288 (O.D. Ø12, I.D. Ø8.8)
Color	N (Translucent)
Roll Length	20 m Roll
-	Air
Maximum operating pressure	0.8 MPa

Additional information

Catalogue

[T_EU.pdf](#)