



verso adjustable height storage bench with 3 drawer cabinet / full cupboard. Featuring a robust, steel channel, adjustable height framework with integrated storage units and a 30mm multiplex wood worktop. Delivered assembled. Integrated cabinet sizes - WxDxH: (2x)525x550x600mm. Drawer configuration: 1x 125mm, 2x 175mm with 100% extension slides (75kg U.D.L.) and a single reinforced door. Finished in durable powder coat paint in RAL 7035 light grey / RAL 7035 light grey. WxDxH: 1250x600x830-930mm.

Breite [mm]: 1250
Tiefe [mm]: 600
Höhe [mm]: 930
Bruttogewicht [kg]: 97.44
EAN-Code: 5039350102244
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Light grey
Main RAL colour	RAL 7035
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schubladen

Number of drawers	3
Drawer load capacity [kg]	75
Drawer height 1 [mm]	125
Drawer height 2 [mm]	175
Drawer height 3 [mm]	175

Schrank, Gehäuse, Werkbank und EAP

Height adjustment range [mm]	830-930
Worktop/housing top type	Beech Multiplex
Door type	Plain
Door height 1 [mm]	475