

### Main

Range of product	Odace
Product or component type	Telephone socket
Device presentation	Mechanism with fixing frame
Telephone socket type	France Telecom (8 contacts)
Type of packing	Paint cover
Quantity per set	Set of 10





### Complementary

Device mounting	Flush
Fixing mode	By screws
Colour tint	Aluminium
Surface finish	Matt
Connections - terminals	Screw terminals
Number of loop terminals	1
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame
Height	71 mm
Width	71 mm
Depth	27.7 mm
Embedding depth	11.7 mm
Net weight	0.037 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

### Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Standards	CENET 28417 Ed3 EN 60529
IK degree of protection	IK04
IP degree of protection	IP21D

Offer Sustainability

REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#"> EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#"> Yes</a>
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>