

42373

Dish Brush with scraping
edge, 280 mm, Medium,
Blue



This Utility Brush is ideal for detail cleaning of machinery and equipment.

Technical Data

Item Number	42373
Visible bristle length	23 mm
Material	Polypropylene Polyester Stainless Steel (AISI 304)
Complies with (EC) 1935/2004 on food contact materials¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	20 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	2200 Pcs.
Quantity Per Layer (Pallet)	200 Pcs.
Box Length	325 mm
Box Width	240 mm
Box Height	170 mm
Length/Depth	280 mm
Width	60 mm
Height	55 mm
Gross Weight	0,08 kg
Net Weight	0,05 kg
Cubik metre	0,001 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature³	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
GTIN-13 Number	5705020423734
GTIN-14 Number (Box quantity)	15705020423731
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care

units, before use.

1. See Declaration of Compliance for further details on food contact

3. Do not store the product below 0° Celsius.