

Previously known as: MICROGARD® 2000 Apron - Model 213

## Protective apron designed with microporous laminate material, for advanced safety and breathable comfort

- **Specialized protection:** This AlphaTec® apron ensures barrier protection and resists saturation when confronted with low-concentration liquid chemicals, liquid and particulate\* biological hazards
- **Heightened breathability:** The use of microporous laminate technology in its fabrication makes for a protective apron that enables water vapor (perspiration) to escape easily
- **Reduced contamination risks:** Due to the low-linting nature of this protective apron's microporous polyethylene laminate nonwoven material, potential contamination risks are also reduced
- **Optimized fit:** It is also designed to offer wearers a perfect combination of fit, comfort and personal protection

\*filters 100% of particulates down to 0.01 microns in size

### Industries

- Life Sciences
- Metal fabrication
- Food Processing

### Applications

- Clean room cleaning and preparing
- Production line support & maintenance
- Maintenance of plant and machines
- Veterinary Services
- Cleaning of plant and machines
- Body painting including surface inspection



# AlphaTec®

ADVANCED CHEMICAL PROTECTION

## 2000 Apron - Model 213

Superior breathable microporous laminate technology

Previously known as: MICROGARD® 2000 Apron - Model 213

### PRODUCT INFORMATION



- **Protective barrier:** Low-concentration liquid chemicals, liquid and particulate biohazards
- **Low-linting microporous laminate:** Breathable comfort with lower contamination risks
- **Optimized fit:** An ideal balance of comfort and safety

### Specifications

STYLE	DESCRIPTION	PACKAGE
AlphaTec® 2000 STANDARD Apron Stitched - Model 213	Microporous polyethylene Laminate non-woven	Individually packaged

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
63000 Cyberjaya  
Selangor, Malaysia  
T: +603 8310 6688  
F: +603 8310 6699

#### Canada

Ansell Canada Inc.  
105, rue Lauder  
Cowansville (Québec)  
J2K 2K8, Canada  
T: 1 800 363-8340  
F: 1 888 267-3551

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Russia

Ahcenn PYC  
123610 Poccnr, Mockba  
Kpachonpechehckar  
Ha6. 12, n.3, op. 1304A  
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

