



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	XCRZ
Product compatibility	XCKMR XCRA XCRB XCKVR
Movement of operating head	Rotary
Type of operator	Square rod metal square rod 6 mm, L = 200 mm
Switch actuation	By any moving part
Type of approach	Lateral approach
Positive opening	With

Complementary

Associated complete product	XCKMR54D1 XCKMR54D1H29 XCKMR54D2 XCKMR54D2H29 XCRA11 XCRA12 XCRA15 XCRA51 XCRA52 XCRA55 XCRB11 XCRB12 XCRB15 XCRB51 XCRB52 XCRB55 XCKMR24SR1H29 XCKMR44D1H29 XCKMR44D2H29
-----------------------------	---

XCKVR24SR1H29
XCKVR44D1H29
XCKVR44D2H29
XCKVR54D1H29
XCKVR54D2H29

Product weight	0.019 kg
----------------	----------

Environment

Ambient air temperature for operation	-25...70 °C
---------------------------------------	-------------

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 0903 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------
