

## Product Information

**FTP100x40-Ø15 NL40**

EAN 4031582329360

Wheel centre made of cast iron, Tread:  
Polyurethane, casted, precision ball bearing

Wheel diameter	100 mm
Width of Tread	40 mm
Axle Hole Ø	15 mm
Hub length	40 mm
Temperature	- 20 / + 60 °C
Standard	EN 12533
Dynamic Load capacity	350 kg
Static Load capacity	700 kg
Hardness of tread	A 92 Shore

