
## coupling socket NPHS-D6-P-G14F Part number: 8059271





## **Data sheet**

Feature	Value
Operating pressure complete temperature range	-0.95 10 bar
Standard nominal flow rate	1,800 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 60 °C
Product weight	124 g
Pneumatic connection, port 1	Female thread 1/4
Materials note	Conforms to RoHS