



CJ1W-DA08V

Analog output unit, 8 x output 1 to 5 V, 0 to 5 V, 0 to 10 V, -10 to 10 V, resolution 1:4000 scalable to ± 32000 or 1:8000, screw terminal

Specifications

I/O system	CJ I/O Bus
Expansion unit type	Special I/O Unit
Type of module	Analog I/O
Number of analog inputs	0
Temperature input type	None
Linear analog input type	None
Number of analog outputs	8
Linear analog output type	-10 to 10 V, 0 to 10 V, 0 to 5 V, 1 to 5 V
Resolution of the analog outputs	12 Bit
Conversion time	4000 ms/unit
I/O connection type	Screw
Number of I/O connectors	1
Detachable I/O connector	✓
Suitable for safety functions	✗
Product Height (unpacked)	90 mm
Product Width (unpacked)	31 mm
Product Depth (unpacked)	89 mm
Product Weight (unpacked)	140 g

CAD Library



CJ-Series Analog I/O Units for NJ-Series (CJ1W-AD0, -DA0, -MAD42)

Operation Manual

EN PDF 6.1 MB



CJ1W-AD0 1-V1 - DA0 1 -DA08 - MAD42(IOWiringDiagram)

Instruction Sheet

EN PDF 59.7 KB



CJ2-Series Programmable Controller

Datasheet

EN PDF 17.9 MB



CS1/CJ1 Analog I/O Units

Operation Manual

EN PDF 4.85 MB



EAC Mark removal Discontinuation Notice

EN PDF 221 KB