

213.53.063 1.6 bar G1/4B lower mount

Bourdon tube pressure gauges, liquid filled,

Item number: 9021957

Quantity: 1 pcs.

Order code: 213.53-C-BG316Z-GB-UZZZ-ZZZ 53 31ABZNZA ZA-ZZ1
DIAL-IAZ1ZZZZZZZZZ1Z- 1Z11Z4ZZZZ
LABEL-E01DE-ZZZZZ

Overview: 213.53.063 1.6 bar G1/4B lower mount
class 1.6
Window: plastic, clear
Case filling fluid: glycerine
standard packing
stop-pin at zero
S *EN 837-1* *Cl.1.6* *WIKA*

Details: Bourdon tube pressure gauges, liquid filled,
stainless steel case, model 213.53.050/063
Model: 213.53
Specifications according to data sheet: PM 02.12
Measuring system: copper alloy
Case: stainless steel 1.4301
Case: Crimp ring case (version 53)
Nominal size: 063 mm
Scale range: 0...1.6 bar
Process connection: G 1/4 B
Connector location: lower mount
Accuracy class: class 1.6
Overpressure safe: standard
Case filling fluid: glycerine
Pointer: plastic, black
Window: plastic, clear
Packaging: standard packing
Dial: plastic, white, with stop-pin
Dial description:
Pressure Gauge Standard: International (standard Europe)
color for 1.scale (outside): black
dial background: White
Manufacturer logo: *WIKA*
stop pin on dial: at zero
norm-mark on dial: *EN 837-1*
safetymark on dial: *S*
accuracy class on dial: *Cl.1.6*