

42JT VisiSight Teach 20mm Miniature Rectangular

[42JT-B2LAT1-F4](#)



Representative Rendering, Not The Actual Product

PHOTOSWITCH Photoelectric Sensor, VisiSight Teach, Background Suppression, Red, DC - LO or DO selectable, Auto Source (PNP) / Sink (NPN), 4-pin DC Micro QD on 152mm (6in) pigtail, IO-Link Enabled

Product Details

PHOTOELECTRIC SENSOR DATA	
Sensing Mode	Background Suppression
Light Source	Visible Red LED
Operating Voltage/Mode	DC - LO or DO selectable
OutputType	Auto Source (PNP) / Sink (NPN)
Sensitivity Adjustment	Push button or Remote Teach
Sensing Range	1 ... 180mm (0.04 ... 7.1 in.)
Connection Type	4-pin DC Micro QD on 152mm (6in) pigtail
IO Link Enabled	Yes
ACCESSORY ITEMS	
Connection Media	DC Micro(M12), Female, Straight, 4-pin PVC, Yellow, Unshielded, 5 m