

Features

- Dual snap-locking
- Small mounting holes
- Ideal when space is restricted

RS PRO PCB Spacers

RS Stock No.: See table



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- Mini locking support posts provide secure fixings for printed circuit boards
- Small mounting holes (2.54mm), ideal when space is restricted
- Simple snap-lock design means no installation tooling required

Material Specifications

Materials	Nylon 66
Type	Snap-In Spacers
Colour	Natural
Flammability Rating	UL94-V2
Working Temperature Range	-40°C to +85°C

Part Specifications

Parameters	0304281	0304283	0304284	0304110	0304111	0304112	0304114	0304115	0304117	0304118
Body Height (A)	3.2mm	4.8mm	6.4mm	7.9mm	9.5mm	11.1mm	12.7mm	14.3mm	15.9mm	22.2mm
PCB Hole Dia	2.54mm	2.54mm	2.54mm	2.54mm	2.54mm	2.54mm	2.54mm	2.54mm	2.54mm	2.54mm
PCB Thickness	1.63mm	1.63mm	1.63mm	1.63mm	1.63mm	1.63mm	1.63mm	1.63mm	1.63mm	1.63mm
Panel Hole Dia	2.54mm	2.54mm	2.54mm	2.54mm	2.54mm	2.54mm	2.54mm	2.54mm	2.54mm	2.54mm
Panel Th'kness	1.63mm	1.63mm	1.63mm	1.63mm	1.63mm	1.63mm	1.63mm	1.63mm	1.63mm	1.63mm

