

FEATURES

- **2 x 3W LED
3.6V 600mAh NiCd**
- **Total lumen output
340lm**
- **Lamps ok status and
Charge indicators**
- **3-hour non-
maintained
operation on battery
power**
- **Polycarbonate IP65
body**
- **Lightweight, only
2.8Kg**
- **IP65 rated -
protected against
dust**

LED Emergency Lighting Twin Spot 2 x 3 W

RS Stock No.: 795-9766



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This IP65 LED non-maintained twin-spot luminaire features a lightweight polycarbonate body with twin-spots LED lamps. This LED emergency luminaire offers an energy saving and cost effective solution to fulfil emergency lighting requirements. Ideal for places requiring an emergency lighting supply like industrial units and warehouses.

General Specifications

Lamp Type	LED
Luminosity	340lm
Maintained	Non Maintained
Material	Polycarbonate
Finish	White
Duration	3h
Lamp Supplied	Yes
Applications	LED emergency exit signs are ideal for commercial, industrial and retail applications and can be found in: Corridors, Workshops

Electrical Specifications

Wattage	2 x 3W
Voltage Rating	230V
Battery	2 x 10W REMOTE HEADS & BATTERY

Mechanical Specifications

Length	300mm
Width	297mm
Depth	73mm
Fitting Type	Twin Spot
Weight	2.8kg

Operation Environment Specifications

Environment Temperature	0°C to 40°C
-------------------------	-------------

Protection Category

IP Rating	IP20
-----------	------

Approvals

Compliance/Certifications	RoHS
Standards Mets	BS5266



