

DWE4217KD-QS

Meuleuse 125 mm 1200W



5035048464564

Product Description:

Disc Ø (mm): 125 Power: 1200W No-load Temperature (RPM): 0-11000 Spindle Thread: M14 Vibration Level (m/s²): 6.2 Switch: Slide



Product features and benefits:

- Low-profile gearbox for working in limited spaces An even stronger motor to meet the most demanding applications
- more demanding.
- Motor protected against dust particle abrasion for longer life Soft start provides more safety and control
- Inductor with connecting wires directly from the winding, for a longer tool life Shaft locking system on the side, allows you to work
- in tight spaces New disc clamping system, prevents jamming Protective guard can be adjusted quickly, without tools The anti-restart system prevents the machine from accidentally restarting after a power outage.
- The switch must be returned to the initial position before the engine can be restarted. Rubberized handles for a better grip Self-rotating carbons for longer motor life Dust ejection system, removes most debris,
- protects motor from particles
-
-

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Service Key (x1)
- Tool-free guard (x1)
- Indoor/Outdoor Flange (x1)
- Set (x1) Multi-position side handle
- (x1) Diamond disc (x1)
-

Specifications techniques :

- Power supply: 1200
- In
- Diameter: 125 mm
- [Imperial] Disc: 5 in
- Diameter: 125 mm
- [Imperial] Diameter: 5 in
- - Disc diameter: 125 mm

