

4-1671000-4

Fiber Optic Termination Panel, 1U, 19 in, LC/UPC, singlemode, black

Product Classification

| | |
|-----------------------|-------------------------|
| Portfolio | NETCONNECT® |
| Product Type | Fiber termination panel |
| Regional Availability | Asia |

Body Features

| | |
|---------------|---------------|
| Chassis Color | Black |
| Finish | Powder coated |

Configuration Features

| | |
|----------------------|---------------|
| Front Connector Type | LC/UPC |
| Configuration | Adapters only |
| Number of Fibers | 48 |
| Port Style | Duplex |

Dimensions

| | |
|--------|----------------------|
| Height | 44.45 mm 1.75 in |
| Width | 482.60 mm 19.00 in |

Packaging Features

| | |
|--------------------|--|
| Includes | Installation Instruction Mounting hardware |
| Packaging Method | Box/Carton |
| Packaging Quantity | 1 |

Product Type Features

| | |
|--------------|------------|
| Rack Units | 1.0 |
| Optical Mode | Singlemode |

Regulatory Compliance/Certifications

| Agency | Classification |
|-----------------|----------------|
| RoHS 2011/65/EU | Compliant |