



 PRODUCT-DETAILS

AL34/M32/A/BL

STR PA66 FITTING M32 34MM-BL



General Information

Extended Product Type	AL34/M32/A/BL
Product ID	7TCA296000R0957
EAN	5020963001543
Catalog Description	STR PA66 FITTING M32 34MM-BL
Long Description	Straight Conduit Fitting, Panel Mount Flange, Fixed External Male Thread, Nominal Conduit Size 34mm, M32 Thread, Polyamide (Nylon) 66, Black

Additional Information

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

Ordering

EAN	5020963001543
UPC	786210280547

Technical

Number of Batteries	0
Color	Black
Material	Polyamide/Nylon 6.6
Size	NC 34mm

Environmental

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963001543
Package Level 1 Height	2.1 in 53 mm
Package Level 1 Depth / Length	0.75 in 19 mm
Package Level 1 Width	1.6 in 41 mm

Certificates and Declarations

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

External Classifications and Standards

ETIM 8	EC001176 - Screw connection for corrugated plastic hose
ETIM 9	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

