

Features

- Proof load tested to $3.5 \times \text{WLL}$ and inspected before dispatch.
- Equipped with powerful Neodymium permanent magnets.
- Lightweight and Compact – Easy to handle and operate.
- Designed to lift both flat and circular steel surfaces.
- Powder-coated steel housing with machined connection surface.
- Chrome-plated shackle for top connection.
- Positive locking device with double locking mechanism.
- Temperature Range – Operates from -40°C to $+80^{\circ}\text{C}$.
- CE-marked, EN 13155, AS 4991.

RS PRO Permanent Lifting Magnet, 600 kg Capacity

RS Stock No.: 0712616



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO Permanent Lifting Magnet is a robust and efficient solution for lifting steel plates and components. Featuring powerful Neodymium magnets, this lightweight device offers exceptional lifting capacity and versatility for both flat and circular surfaces. Its durable powder-coated housing, chrome-plated shackle, and advanced safety locking system ensure reliable performance in demanding environments. Fully compliant with EN 13155 and AS 4991 standards, this lifting magnet delivers superior safety and long-term reliability.

General Specifications

Lifting Capacity (WLL)	600 kg
Type	Permanent Lifting Magnet
Material	High-quality magnetic material in steel housing
Finish	Red powder-coated housing, chrome-plated shackle
Temperature Range	-40°C to +80°C
Safety Factor	3.5:1
Note	Max capacity based on clean, flat, low-carbon steel

Approvals

Standards Met	EN 13155, AS 4991, CE-marked
---------------	------------------------------

Similar Products

Stock No.	Brand	Product Name	Load Capacity	Lift Height	Overload Protection
0712607	RS PRO	Lever Hoist	250 kg	1.5 m	-
0712608	RS PRO	Chain Block	2000 kg	3.0 m	Yes
0712609	RS PRO	Chain Block	500 kg	3.0 m	Yes
0712610	RS PRO	Lever Hoist	1600 kg	1.5 m	Yes
0712611	RS PRO	Lever Hoist	800 kg	1.5 m	Yes
0712612	RS PRO	Chain Block	1000 kg	3.0 m	Yes
0712613	RS PRO	Push Trolley	1000 kg	Fits I-Beams	-
0712614	RS PRO	Lever Hoist	500 kg	1.5 m	Yes
0712615	RS PRO	Lever Hoist	3200 kg	1.5 m	Yes
0712616	RS PRO	Lifting Magnet	Lifting Capacity: 600 kg	-	-