



# Product Information & News

## Vara Room Sounder

Part no: VRS-1-W (white) & VRS-1-R (red)


### Description

The new Vara room sounder is ideal for applications where a discrete sounder is required that meets the requirements of BS 5839.


Utilising a new nose cone that reflects sound back onto the front plate, the Vara bedhead sounder gives a wide distribution of sound and may be used in corridors where a more dispersed sound is required.

Each Vara sounder has a choice of four tones including Warble, Sweep and Pips selected from a jumper fitted to the pcb. The Continuous tone is selected via the terminal array and is also used as a second stage alarm if a third wire is fitted.

### Dimensions



### Installation Details



### Technical Details

Sound Output @ 1 metre (26v dc)	:	97 dB(a)
Current Consumption @ 26v dc	:	c.30 mA
Voltage Range	:	8-35v dc
Number of Tones	:	4
Volume Control	:	-30 dB(a)
Weatherproofing	:	IP 42
Weight (per unit packed)	:	140g

Cranford Controls Ltd Unit A1 Blacknest Industrial Estate Blacknest Alton Hants GU34 4PX  
Tel: +44 (0) 1420 520520 Fax: +44 (0) 1420 520521 E-mail [sounder@cclb.demon.co.uk](mailto:sounder@cclb.demon.co.uk)

REF:2704/2 Issue 2